

HUBBELL

Power Systems

SDC™ Composite Bushing - 25KV

By Electro Composites
 Catalog # [150-100-G-897-00](#)

SDC™ 25kV-10000A GSU Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 21.0" Min.Oil Immersion Level/CT Pocket, 24.9" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-15NA High Temperature Cycloaliphatic Epoxy Compound for high temperature applications
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEEE C57.19.01/C57.19.04 Electrical and Mechanical Requirements

General

Application	GSU
Bottom Terminal Type	2X Blades With 6X 0.69 Dia Holes
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-15NA - High Temp Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Bolt Holes - Bottom Terminal	6
Number of Bolt Holes - Top Terminal	32
Number of Flange Mounting Holes	8
Plating - Bottom Terminal	Silver
Test Tap	Yes
Top Terminal Plating	Silver
Top Terminal Type	4X Blades With 8X 0.69 Dia Holes
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	18.1 in
Below Flange Length	32.5 in
Diameter - Above Flange Maximum	13.00 in
Diameter - Below Flange Maximum D <gt;/> 1"	9.75 in
Diameter - Below Flange Maximum P	9.75 in
Diameter - Live Part Bottom	9.75 in
Diameter - Live Part Top	11.66 in
Dimensions	50.60 in x 17.25 in x 17.25 in
Effective Length - Bottom Terminal	4.15 in
Effective Length - Top Terminal	3.88 in
Flange Mounting Hole Bolt Circle	15.75 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	17.25 in
Height	17.25 in
Length	50.6 in
Length - Drawlead Above Flange	NA
Length - Ground Shield	21.00 in
Length - Insulation Above Flange	9.80 in
Length - Insulation Below Flange	26.70 in
Length - Live Part Bottom	5.80 in
Length - Live Part Top	4.80 in
Length - Minimum Oil Immersion Level	21.00 in
Sealing Surface Inside Diameter	9.87 in
Sealing Surface Outside Diameter	14.87 in
Top Terminal Min. Thread Length	3.88 in
Weight	346 lb
Width	17.25 in

Electrical Ratings

BIL	150 kV
Current Rating	10000 A
Minimum Creepage	24.9 in
Minimum Creepage - Inside	NA
Minimum Strike	10.1 in
Minimum Strike - Inside	NA
Withstand Voltage - 60 Hz Dry	60 kV
kV Class	25 kV

Certifications And Compliance

Industry Standard(s)	IEEE C57.19.01/C57-19.04
----------------------	--------------------------

Product Assets

- [Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
- [Literature - SDC™ HV Generator Bushings - Electro Composites](#)
- [Sales Drawings - SDC GSU Bushing 25kV, 10,000A Model: 150-100-G-897-00](#)
- [Video - ElectroComposites Factory Tour: St. Jerome](#)