

SDC™ Composite Bushing - 35kV

By Electro Composites
Catalog # 200-012-B-066-06

SDC™ 35kV-1200 A OCB Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per CSA C88.1, Bottom Connected for Air-to-Oil Applications, 17" Min. Oil Immersion Level/CT Pocket Length, 30.6" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- Meets CSA C88.1 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

Application

OCB

General

Bottom Terminal Type	2.36 DIA SMOOTH WITH 1X GROOVE
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	19.5 in
Below Flange Length	31.5 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	3.12 in
Diameter - Below Flange Maximum P	3.88 in
Diameter - Live Part Bottom	2.36 in
Diameter - Live Part Top	3.00 in
Effective Length - Bottom Terminal	3.00 in
Effective Length - Top Terminal	3.00 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	8.50 in
Length	51.00 in
Length - Ground Shield	17.00 in
Length - Insulation Above Flange	11.30 in
Length - Insulation Below Flange	10.20 in
Length - Live Part Bottom	4.30 in
Length - Live Part Top	4.40 in
Length - Minimum Oil Immersion Level	17.00 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	6.37 in
Top Terminal Min. Thread Length	3.00 in
Weight	61 lb

Electrical Ratings

BIL	200 kV
Current Rating	1200 A
Minimum Creepage	30.60 in
Minimum Strike	13.70 in
Withstand Voltage - 60 Hz Dry	95 kV
kV Class	35 kV

Certifications and Compliance

Industry Standard(s)

CSA C88.1

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
[Literature - Apparatus Bushings Selection Guide \(TD02026E\)](#)
[Literature - SDC™ GSU Bushings - Electro Composites \(SF02018E\)](#)
[Literature - SDC™ HV Generator Bushings - Electro Composites \(SF02019E\)](#)
[Literature - SDC™ HV Bushings - Electro Composites \(SF02017E\)](#)
[Literature - EC SDC Solid Dielectric Bushings v3](#)
[Literature - FRENCH V2 - EC Generation Bushings](#)
[Literature - FRENCH V2 - EC GSU Bushings](#)
[Literature - How an SDC Bushing Test Tap is Constructed](#)
[Sales Drawings - 066-06_6640-10065](#)
[Video - ElectroComposites Factory Tour: St. Jerome \(V100124E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
EC-200-012-B-066-06-SPEC-EN | REV 1/2024