

## SDC™ Composite Bushing - 35kV

By Electro Composites  
Catalog # 200-012-T-626-01

SDC™ 35kV-1200 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEC 60137, Bottom Connected for Air-to-Oil Applications, 10" Min. Oil Immersion Level/CT Pocket Length, 38.2" Min. Creepage Length



\*Representative Image

### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- Meets IEC 60137 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

### Application

Transformer

### General

Bottom Terminal Type	1 1/2-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	Tin
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

### Dimensions

Above Flange Length	26.55 in
Below Flange Length	20.75 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	4.15 in
Diameter - Below Flange Maximum P	4.26 in
Diameter - Live Part Bottom	1.50 in
Diameter - Live Part Top	3.00 in
Effective Length - Bottom Terminal	2.50 in
Effective Length - Top Terminal	4.00 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.63 in
Flange Outside Diameter	8.50 in
Length	47.30 in
Length - Ground Shield	10.00 in
Length - Insulation Above Flange	18.20 in
Length - Insulation Below Flange	6.85 in
Length - Live Part Bottom	3.90 in
Length - Live Part Top	4.80 in
Length - Minimum Oil Immersion Level	10.00 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	6.62 in
Top Terminal Min. Thread Length	4.00 in
Weight	71 lb

### Electrical Ratings

BIL	200 kV
Current Rating	1200 A
Minimum Creepage	38.20 in
Minimum Strike	20.50 in
Withstand Voltage - 60 Hz Dry	95 kV
kV Class	35 kV

## Certifications and Compliance

Industry Standard(s)

IEC 60137

### Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)  
[Literature - Apparatus Bushings Selection Guide \(TD02026E\)](#)  
[Literature - SDC™ GSU Bushings - Electro Composites \(SF02018E\)](#)  
[Literature - SDC™ HV Generator Bushings - Electro Composites \(SF02019E\)](#)  
[Literature - SDC™ HV Bushings - Electro Composites \(SF02017E\)](#)  
[Literature - EC SDC Solid Dielectric Bushings v3](#)  
[Literature - FRENCH V2 - EC Generation Bushings](#)  
[Literature - FRENCH V2 - EC GSU Bushings](#)  
[Literature - How an SDC Bushing Test Tap is Constructed](#)  
[Sales Drawings - 626-01\\_7349-7059](#)  
[Video - ElectroComposites Factory Tour: St. Jerome \(V100124E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
EC-200-012-T-626-01-SPEC-EN | REV 1/2024