

# HUBBELL

## Power Systems

### SDC™ Composite Bushing - 26.4kV

By Electro Composites  
 Catalog # [150-063-G-653-01](#)

SDC™ 26.4kV-6300 A GSU Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEC 60137, Bottom Connected for Air-to-Oil Applications, 10" Min. Oil Immersion Level/CT Pocket Length, 37" Min. Creepage Length



\*Representative Image

#### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-15NA High Temperature Cycloaliphatic Epoxy Compound for high temperature applications
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEC 60137 Electrical and Mechanical Requirements

#### General

Application	GSU
Bottom Terminal Type	1x Blade with 6x 0.69 Dia Holes
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-15NA - High Temp Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Bolt Holes - Bottom Terminal	6
Number of Bolt Holes - Top Terminal	24
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	Silver
Test Tap	Yes
Top Terminal Plating	Silver
Top Terminal Type	4x Blades with 6x 0.69 Dia Holes
Type	SDC - Solid Dielectric Capacitor

#### Dimensions

Above Flange Length	22.38 in
Below Flange Length	21.5 in
Diameter - Above Flange Maximum	13.00 in
Diameter - Below Flange Maximum D <gt;/> 1"	8.38 in
Diameter - Below Flange Maximum P	8.91 in
Diameter - Live Part Bottom	8.38 in
Diameter - Live Part Top	9.91 in
Dimensions	43.88 in x 14.75 in x 14.75 in
Effective Length - Bottom Terminal	4.28 in
Effective Length - Top Terminal	3.88 in
Flange Mounting Hole Bolt Circle	13.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	14.75 in
Height	14.75 in
Length	43.88 in
Length - Ground Shield	10.00 in
Length - Insulation Above Flange	14.10 in
Length - Insulation Below Flange	5.72 in
Length - Live Part Bottom	5.78 in
Length - Live Part Top	4.80 in
Length - Minimum Oil Immersion Level	10.00 in
Sealing Surface Inside Diameter	9.87 in
Sealing Surface Outside Diameter	12.37 in
Weight	269 lb
Width	14.75 in

## Electrical Ratings

BIL	150 kV
Current Rating	6300 A
Minimum Creepage	37 in
Minimum Strike	15 in
Withstand Voltage - 60 Hz Dry	55 kV
kV Class	26.4 kV

## Certifications And Compliance

Industry Standard(s)	IEC 60137
----------------------	-----------

## Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 653-01\\_6776-8192](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand