

HUBBELL

Power Systems

SDC™ Composite Bushing - 25kV

By Electro Composites
 Catalog # [150-140-G-509-00](#)

SDC™ 25kV-14000 A GSU Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 21" Min. Oil Immersion Level/CT Pocket Length, 22.7" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-15NA High Temperature Cycloaliphatic Epoxy Compound for high temperature applications
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEEE C57.19.01/C57.19.04 Electrical and Mechanical Requirements

General

Application	GSU
Bottom Terminal Type	2X BLADES WITH 6X 0.69 DIA HOLES
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-15NA - High Temp Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Bolt Holes - Bottom Terminal	12
Number of Bolt Holes - Top Terminal	40
Number of Flange Mounting Holes	12
Plating - Bottom Terminal	Silver
Test Tap	Yes
Top Terminal Plating	Silver
Top Terminal Type	4X BLADES WITH 10X 0.69 DIA HOLES
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	18.1 in
Below Flange Length	32.53 in
Diameter - Above Flange Maximum	15.75 in
Diameter - Below Flange Maximum D <gt;/> 1"	12.50 in
Diameter - Below Flange Maximum P	12.50 in
Diameter - Live Part Bottom	12.50 in
Diameter - Live Part Top	13.81 in
Dimensions	50.63 in x 20.00 in x 20.00 in
Effective Length - Bottom Terminal	4.06 in
Effective Length - Top Terminal	3.88 in
Flange Mounting Hole Bolt Circle	18.5 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	20 in
Height	20 in
Length	50.63 in
Length - Ground Shield	21.00 in
Length - Insulation Above Flange	9.90 in
Length - Insulation Below Flange	5.63 in
Length - Live Part Bottom	5.90 in
Length - Live Part Top	4.70 in
Length - Minimum Oil Immersion Level	21.00 in
Sealing Surface Inside Diameter	13.11 in
Sealing Surface Outside Diameter	17.62 in
Weight	473 lb
Width	20 in

Electrical Ratings

BIL	150 kV
Current Rating	14000 A
Minimum Creepage	22.7 in
Minimum Strike	10.5 in
Withstand Voltage - 60 Hz Dry	60 kV
kV Class	25 kV

Certifications And Compliance

Industry Standard(s) IEEE C57.19.01/C57-19.04

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 509-00_5955-5588](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand