

# HUBBELL

## Power Systems

### SDC™ Composite Bushing - 34.5kV

By Electro Composites  
 Catalog # [200-023-T-686-02](#)

SDC™ 34.5kV-2350 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 21" Min. Oil Immersion Level/CT Pocket Length, 54.8" Min. Creepage Length



\*Representative Image

#### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-15NA High Temperature Cycloaliphatic Epoxy Compound for high temperature applications
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements

#### General

Application	Transformer
Bottom Terminal Type	1 1/2-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-15NA - High Temp Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	Silver
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

#### Dimensions

Above Flange Length	25.6 in
Below Flange Length	32.5 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	3.12 in
Diameter - Below Flange Maximum P	4.05 in
Diameter - Live Part Bottom	1.50 in
Diameter - Live Part Top	3.00 in
Dimensions	58.13 in x 8.50 in x 8.50 in
Effective Length - Bottom Terminal	3.25 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	8.5 in
Height	8.5 in
Length	58.13 in
Length - Ground Shield	21.00 in
Length - Insulation Above Flange	18.20 in
Length - Insulation Below Flange	6.30 in
Length - Live Part Bottom	5.20 in
Length - Live Part Top	3.70 in
Length - Minimum Oil Immersion Level	21.00 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	6.37 in
Top Terminal Min. Thread Length	2.5 in
Weight	74 lb
Width	8.5 in

## Electrical Ratings

BIL	200 kV
Current Rating	2350 A
Minimum Creepage	54.8 in
Minimum Strike	20.7 in
Withstand Voltage - 60 Hz Dry	80 kV
kV Class	34.5 kV

## Certifications And Compliance

Industry Standard(s) IEEE C57.19.01

## Product Assets

[Catalogs - Electro Composites SDC™ composite bushings](#)  
[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)  
[Sales Drawings - 686-02\\_3691-8692](#)  
[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
EC-200023T68602-SPEC-EN | REV 6/2024