

HUBBELL

Power Systems

SDC™ Composite Bushing - 34.5kV

By Electro Composites
 Catalog # [200-025-B-562-02](#)

SDC™ 34.5kV-2500 A OCB Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 21" Min. Oil Immersion Level/CT Pocket Length, 37.6" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements

General

Application	OCB
Bottom Terminal Type	2-12 WITH 1X GROOVE
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	2-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	21.88 in
Below Flange Length	31.5 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	4.15 in
Diameter - Below Flange Maximum P	4.15 in
Diameter - Live Part Bottom	2.00 in
Diameter - Live Part Top	3.50 in
Dimensions	53.38 in x 9.50 in x 9.50 in
Effective Length - Bottom Terminal	2.50 in
Effective Length - Top Terminal	3.50 in
Flange Mounting Hole Bolt Circle	8.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	9.5 in
Height	9.5 in
Length	53.38 in
Length - Ground Shield	21.00 in
Length - Insulation Above Flange	13.50 in
Length - Insulation Below Flange	7.10 in
Length - Live Part Bottom	3.40 in
Length - Live Part Top	4.60 in
Length - Minimum Oil Immersion Level	21.00 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	7.37 in
Top Terminal Min. Thread Length	3.5 in
Weight	99 lb
Width	9.5 in

Electrical Ratings

BIL	200 kV
Current Rating	2500 A
Minimum Creepage	37.6 in
Minimum Strike	15.7 in
Withstand Voltage - 60 Hz Dry	80 kV
kV Class	34.5 kV

Certifications And Compliance

Industry Standard(s) IEEE C57.19.01

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 562-02_9729-9512](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
EC-200025B56202-SPEC-EN | REV 6/2024