

HUBBELL

Power Systems

SDC™ Composite Bushing - 38kV

By Electro Composites
 Catalog # [200-006-T-127-01](#)

SDC™ 38kV-600 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEC 60137, Bottom Connected for Air-to-Oil Applications, 9.4" Min. Oil Immersion Level/CT Pocket Length, 26" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEC 60137 Electrical and Mechanical Requirements

General

Application	Transformer
Bottom Terminal Type	1X BLADE WITH 2X 1/2-13 THREADED HOLES
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Stainless Steel
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Bolt Holes - Bottom Terminal	2
Number of Bolt Holes - Top Terminal	2
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	Tin
Test Tap	No
Top Terminal Plating	Tin
Top Terminal Type	1X BLADE WITH 2X 1/2-13 THREADED HOLES
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	15.75 in
Below Flange Length	24.56 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	4.48 in
Diameter - Below Flange Maximum P	5.30 in
Diameter - Live Part Bottom	1.50 in
Diameter - Live Part Top	3.00 in
Dimensions	40.31 in x 11.80 in x 11.80 in
Effective Length - Bottom Terminal	4.13 in
Effective Length - Top Terminal	4.13 in
Flange Mounting Hole Bolt Circle	10.8 in
Flange Mounting Hole Diameter	0.53 in
Flange Outside Diameter	11.8 in
Height	11.8 in
Length	40.31 in
Length - Ground Shield	9.40 in
Length - Insulation Above Flange	9.80 in
Length - Insulation Below Flange	9.86 in
Length - Live Part Bottom	5.30 in
Length - Live Part Top	5.20 in
Length - Minimum Oil Immersion Level	9.40 in
Sealing Surface Inside Diameter	9 in
Sealing Surface Outside Diameter	9.41 in
Weight	71 lb
Width	11.8 in

Electrical Ratings

BIL	200 kV
Current Rating	600 A
Minimum Creepage	26 in
Minimum Creepage - Inside	24.50 in
Minimum Strike	11.9 in
Minimum Strike - Inside	18.30 in
Withstand Voltage - 60 Hz Dry	70 kV
kV Class	38 kV

Certifications And Compliance

Industry Standard(s) IEC 60137

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 127-01_7318-6973](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand