

SDC™ Composite Bushing - 35kV

By Electro Composites
Catalog # [200-012-B-066-06](#)

SDC™ 35kV-1200 A OCB Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per CSA C88.1, Bottom Connected for Air-to-Oil Applications, 17" Min. Oil Immersion Level/CT Pocket Length, 30.6" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets CSA C88.1 Electrical and Mechanical Requirements

Application

OCB

General

Bottom Terminal Type	2.360 DIA SMOOTH WITH 1X GROOVE
Catalog Number	200-012-B-066-06
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	19.5 in
Below Flange Length	31.5 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt; 1"	3.12 in
Diameter - Below Flange Maximum P	3.88 in
Diameter - Conductor Outside Under Insulation	1.25 in

Diameter - Live Part Bottom	2.36 in
Diameter - Live Part Top	3.00 in
Diameter - Rod / Tube	1.5 in
Dimensions	51.00 in x 8.50 in x 8.50 in
Effective Length - Bottom Terminal	3.00 in
Effective Length - Top Terminal	3.00 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	8.5 in
Height	8.5 in
Length	51 in
Length - Ground Shield	17.00 in
Length - Insulated Section	42.2 in
Length - Insulation Above Flange	11.30 in
Length - Insulation Below Flange	10.20 in
Length - Live Part Bottom	4.30 in
Length - Live Part Top	4.40 in
Length - Minimum Oil Immersion Level	17.00 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	6.37 in
Thickness	0.935 in
Top Terminal Min. Thread Length	3 in
Weight	61 lb
Width	8.5 in

Electrical Ratings

BIL	200 kV
Current Rating	1200 A
Minimum Creepage	30.6 in
Minimum Strike	13.7 in
Withstand Voltage - 60 Hz Dry kV Class	95 kV
	35 kV

Certifications And Compliance

Industry Standard(s)	CSA C88.1
----------------------	-----------

Product Assets

[Catalogs - Electro Composites SDC™ composite bushings](#)
[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
[Literature - SDC™ HV Generator Bushings - Electro Composites](#)
[Literature - How an SDC Bushing Test Tap is Constructed](#)
[Literature - TRAVERSÉE SDC™ ÉLECTRO COMPOSITES DE TYPE GSU](#)
[Literature - SDC™ GSU Bushings - Electro Composites](#)

[Literature - TRAVERSÉE SDC™ ÉLECTRO COMPOSITES POUR GÉNÉRATEUR](#)
[Literature - Apparatus Bushings Selection Guide](#)
[Literature - ÉLECTRO COMPOSITES TRAVERSÉE HAUTE TENSION SDC™](#)
[Literature - SDC™ HV Bushings - Electro Composites](#)
[Sales Drawings - 066-06_6640-10065](#)
[Specifications - 200012B06606](#)
[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
EC-200012B06606-SPEC-EN | REV 3/2025