

HUBBELL

Power Systems

SDC™ Composite Bushing - 34.5kV

By Electro Composites
Catalog # [200-412-I-538-05](#)

SDC™ 34.5kV-400/1200 A Transformer-Breaker Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom-Drawlead Connected for Air-to-Oil Applications, 21" Min. Oil Immersion Level/CT Pocket Length, 44.4" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements

General

Application	Transformer-Breaker
Bottom Terminal Type	1 1/2-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	Silver
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	25.8 in
Below Flange Length	31.5 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D > 1"	3.48 in
Diameter - Below Flange Maximum P	3.59 in
Diameter - Live Part Bottom	1.50 in
Diameter - Live Part Top	3.50 in
Dimensions	57.25 in x 9.00 in x 9.00 in
Effective Length - Bottom Terminal	2.25 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	9 in
Height	9 in
Length	57.25 in
Length - Drawlead Above Flange	21.75 in
Length - Ground Shield	21.00 in
Length - Insulation Above Flange	15.80 in
Length - Insulation Below Flange	7.00 in
Length - Live Part Bottom	3.50 in
Length - Live Part Top	5.20 in
Length - Minimum Oil Immersion Level	21.00 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	6.37 in
Stud Inside Diameter	0.88 in
Thread Size - Drawlead Connector	3/4-12
Top Terminal Min. Thread Length	2.5 in
Weight	69 lb
Width	9 in

Electrical Ratings

BIL	200 kV
Current Rating	400/1200 A
Minimum Creepage	44.4 in
Minimum Strike	18 in
Withstand Voltage - 60 Hz Dry	80 kV
kV Class	34.5 kV

Certifications And Compliance

Industry Standard(s)	IEEE C57.19.01
----------------------	----------------

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
[Sales Drawings - 538-05_4616-10168](#)