

SDC™ Composite Bushing - 46kV

By Electro Composites
Catalog # 250-004-T-383-00

SDC™ 46kV-400DL/400 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom-Drawlead Connected for Air-to-Oil Applications, 15" Min. Oil Immersion Level/CT Pocket Length, 38" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

Application

Transformer

General

Bottom Terminal Type	1 1/8-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	Silver
Top Terminal Type	1 1/8-12
Type	Condenser Bushings

Dimensions

Above Flange Length	29.13 in
Below Flange Length	26.5 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	4.15 in
Diameter - Below Flange Maximum P	4.15 in
Diameter - Live Part Bottom	1.50 in
Diameter - Live Part Top	3.50 in
Effective Length - Bottom Terminal	2.25 in
Effective Length - Top Terminal	2.25 in
Flange Mounting Hole Bolt Circle	10.88 in
Flange Mounting Hole Diameter	0.56 in
Flange Outside Diameter Length	12.25 in
Length - Drawlead Above Flange	55.63 in
Length - Ground Shield	24.00 in
Length - Insulation Above Flange	15.00 in
Length - Insulation Below Flange	18.11 in
Length - Live Part Bottom	7.70 in
Length - Live Part Top	3.80 in
Length - Minimum Oil Immersion Level	7.07 in
Sealing Surface Inside Diameter	15.00 in
Sealing Surface Outside Diameter	7.50 in
Stud Inside Diameter	9.88 in
Thread Size - Drawlead Connector	0.88 in
Top Terminal Min. Thread Length	3/4-12
Weight	2.25 in
	80 lb

Electrical Ratings

BIL	250 kV
Current Rating	400 A

Minimum Creepage	38.00 in
Minimum Strike	20.00 in
Withstand Voltage - 60 Hz Dry	105 kV
kV Class	46 kV

Certifications and Compliance

Industry Standard(s) IEEE C57.19.01

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
[Literature - Apparatus Bushings Selection Guide \(TD02026E\)](#)
[Literature - SDC™ GSU Bushings - Electro Composites \(SF02018E\)](#)
[Literature - SDC™ HV Generator Bushings - Electro Composites \(SF02019E\)](#)
[Literature - SDC™ HV Bushings - Electro Composites \(SF02017E\)](#)
[Literature - EC SDC Solid Dielectric Bushings v3](#)
[Literature - FRENCH V2 - EC Generation Bushings](#)
[Literature - FRENCH V2 - EC GSU Bushings](#)
[Literature - How an SDC Bushing Test Tap is Constructed](#)
[Sales Drawings - 383-00_5171-4721](#)
[Video - ElectroComposites Factory Tour: St. Jerome \(VI00124E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
EC-250-004-T-383-00-SPEC-EN | REV 1/2024