

SDC™ Composite Bushing - 52kV

By Electro Composites
Catalog # 250-006-T-454-00

SDC™ 52kV-630DL A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEC 60137, Drawlead Connected for Air-to-Oil Applications, 5.9" Min. Oil Immersion Level/CT Pocket Length, 44.8" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- Meets IEC 60137 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

Application

Transformer

General

Bottom Terminal Type	None
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	8
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1.180 DIA SMOOTH
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	30.22 in
Below Flange Length	12.88 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	4.15 in
Diameter - Below Flange Maximum P	4.15 in
Diameter - Live Part Bottom	1.25 in
Diameter - Live Part Top	3.50 in
Effective Length - Top Terminal	3.13 in
Flange Mounting Hole Bolt Circle	9.72 in
Flange Mounting Hole Diameter	0.69 in
Flange Outside Diameter	11.42 in
Length	43.10 in
Length - Drawlead Above Flange	26.00 in
Length - Ground Shield	5.90 in
Length - Insulation Above Flange	20.40 in
Length - Insulation Below Flange	6.18 in
Length - Live Part Bottom	0.80 in
Length - Live Part Top	5.90 in
Length - Minimum Oil Immersion Level	5.90 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	9.03 in
Stud Inside Diameter	1.00 in
Thread Size - Drawlead Connector	3/4-12
Weight	53 lb

Electrical Ratings

BIL	250 kV
Current Rating	630 A
Minimum Creepage	44.80 in
Minimum Strike	22.50 in
Withstand Voltage - 60 Hz Drv	95 kV

Certifications and Compliance

Industry Standard(s)

IEC 60137

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
[Literature - Apparatus Bushings Selection Guide \(TD02026E\)](#)
[Literature - SDC™ GSU Bushings - Electro Composites \(SF02018E\)](#)
[Literature - SDC™ HV Generator Bushings - Electro Composites \(SF02019E\)](#)
[Literature - SDC™ HV Bushings - Electro Composites \(SF02017E\)](#)
[Literature - EC SDC Solid Dielectric Bushings v3](#)
[Literature - FRENCH V2 - EC Generation Bushings](#)
[Literature - FRENCH V2 - EC GSU Bushings](#)
[Literature - How an SDC Bushing Test Tap is Constructed](#)
[Sales Drawings - 454-00_5569-5241](#)
[Video - ElectroComposites Factory Tour: St. Jerome \(V100124E\)](#)



A proud member of the Hubbell Family.