

SDC™ Composite Bushing - 46kV

By Electro Composites
Catalog # 250-012-B-081-00

SDC™ 46kV-1200 A OCB Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE/IEC, Bottom Connected for Air-to-Oil Applications, 20" Min. Oil Immersion Level/CT Pocket Length, 38.3" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- Can be mounted vertically or horizontally

Application

OCB

General

Bottom Terminal Type	1 1/2-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1 1/2-12
Type	Condenser Bushings

Dimensions

Above Flange Length	28.37 in
Below Flange Length	33.5 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt/> 1"	3.74 in
Diameter - Below Flange Maximum P	3.74 in
Diameter - Live Part Bottom	1.50 in
Diameter - Live Part Top	3.00 in
Effective Length - Bottom Terminal	2.38 in
Effective Length - Top Terminal	4.00 in
Flange Mounting Hole Bolt Circle	8.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	9.63 in
Length	61.87 in
Length - Ground Shield	20.00 in
Length - Insulation Above Flange	18.20 in
Length - Insulation Below Flange	10.50 in
Length - Live Part Bottom	3.00 in
Length - Live Part Top	5.30 in
Length - Minimum Oil Immersion Level	20.00 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	7.37 in
Top Terminal Min. Thread Length	4.00 in
Weight	89 lb

Electrical Ratings

BIL	250 kV
Current Rating	1200 A
Minimum Creepage	38.30 in
Minimum Strike	20.50 in
Withstand Voltage - 60 Hz Dry	105 kV
kV Class	46 kV

Certifications and Compliance

Industry Standard(s)

IEEE/IEC

Product Assets

Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites
Literature - Apparatus Bushings Selection Guide (TD02026E)
Literature - SDC™ GSU Bushings - Electro Composites (SF02018E)
Literature - SDC™ HV Generator Bushings - Electro Composites (SF02019E)
Literature - SDC™ HV Bushings - Electro Composites (SF02017E)
Literature - EC SDC Solid Dielectric Bushings v3
Literature - FRENCH V2 - EC Generation Bushings
Literature - FRENCH V2 - EC GSU Bushings
Literature - How an SDC Bushing Test Tap is Constructed
Sales Drawings - 081-00_2256-1398
Video - ElectroComposites Factory Tour: St. Jerome (V100124E)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
EC-250-012-B-081-00-SPEC-EN | REV 1/2024