

HUBBELL

Power Systems

SDC™ Composite Bushing - 34.5kV

By Electro Composites
 Catalog # [200-040-T-487-01](#)

SDC™ 34.5kV-4000 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 21" Min. Oil Immersion Level/CT Pocket Length, 43.5" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements

General

Application	Transformer
Bottom Terminal Type	3-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	Silver
Top Terminal Type	3-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	23.8 in
Below Flange Length	32.5 in
Diameter - Above Flange Maximum	10.13 in
Diameter - Below Flange Maximum D <gt;/> 1"	5.02 in
Diameter - Below Flange Maximum P	5.02 in
Diameter - Live Part Bottom	3.00 in
Diameter - Live Part Top	4.50 in
Dimensions	56.30 in x 11.00 in x 11.00 in
Effective Length - Bottom Terminal	3.00 in
Effective Length - Top Terminal	3.00 in
Flange Mounting Hole Bolt Circle	9.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	11 in
Height	11 in
Length	56.3 in
Length - Ground Shield	21.00 in
Length - Insulation Above Flange	15.90 in
Length - Insulation Below Flange	7.10 in
Length - Live Part Bottom	4.40 in
Length - Live Part Top	3.90 in
Length - Minimum Oil Immersion Level	21.00 in
Sealing Surface Inside Diameter	5.11 in
Sealing Surface Outside Diameter	8.37 in
Top Terminal Min. Thread Length	3 in
Weight	190 lb
Width	11 in

Electrical Ratings

BIL	200 kV
Current Rating	4000 A
Minimum Creepage	43.5 in
Minimum Strike	18.4 in
Withstand Voltage - 60 Hz Dry	80 kV
kV Class	34.5 kV

Certifications And Compliance

Industry Standard(s) IEEE C57.19.01

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 487-01_7901-7332](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
EC-200040T48701-SPEC-EN | REV 6/2024