

HUBBELL

Power Systems

SDC™ Composite Bushing - 35kV

By Electro Composites
 Catalog # [200-050-T-551-00](#)

SDC™ 35kV-5000 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per CSA C88.1, Bottom Connected for Air-to-Oil Applications, 21.7" Min. Oil Immersion Level/CT Pocket Length, 43.5" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets CSA C88.1 Electrical and Mechanical Requirements

General

Application	Transformer
Bottom Terminal Type	1X BLADE WITH 4X 0.69 DIA HOLES
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Bolt Holes - Bottom Terminal	4
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	4-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	25 in
Below Flange Length	34 in
Diameter - Above Flange Maximum	11.13 in
Diameter - Below Flange Maximum D <gt;/> 1"	6.02 in
Diameter - Below Flange Maximum P	6.20 in
Diameter - Live Part Bottom	4.00 in
Diameter - Live Part Top	5.50 in
Dimensions	59.00 in x 12.00 in x 12.00 in
Effective Length - Bottom Terminal	4.25 in
Effective Length - Top Terminal	5.00 in
Flange Mounting Hole Bolt Circle	10.25 in
Flange Mounting Hole Diameter	0.63 in
Flange Outside Diameter	12 in
Height	12 in
Length	59 in
Length - Ground Shield	21.70 in
Length - Insulation Above Flange	15.91 in
Length - Insulation Below Flange	6.92 in
Length - Live Part Bottom	5.38 in
Length - Live Part Top	5.77 in
Length - Minimum Oil Immersion Level	21.70 in
Sealing Surface Inside Diameter	6.24 in
Sealing Surface Outside Diameter	9.62 in
Top Terminal Min. Thread Length	5 in
Weight	302 lb
Width	12 in

Electrical Ratings

BIL	200 kV
Current Rating	5000 A
Minimum Creepage	43.5 in
Minimum Strike	18.4 in
Withstand Voltage - 60 Hz Dry	95 kV
kV Class	35 kV

Certifications And Compliance

Industry Standard(s) CSA C88.1

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 551-00_6171-5814](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand