

SDC™ Composite Bushing - 46kV

By Electro Composites
Catalog # 250-012-T-479-00

SDC™ 46kV-1200 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 26.75" Min. Oil Immersion Level/CT Pocket Length, 35.8" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

Application

Transformer

General

Bottom Terminal Type	1 1/8-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	Silver
Top Terminal Type	1.500 DIA SMOOTH
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	23.31 in
Below Flange Length	40.38 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	4.15 in
Diameter - Below Flange Maximum P	4.15 in
Diameter - Live Part Bottom	1.50 in
Diameter - Live Part Top	3.00 in
Effective Length - Bottom Terminal	2.88 in
Effective Length - Top Terminal	3.36 in
Flange Mounting Hole Bolt Circle	10.88 in
Flange Mounting Hole Diameter	0.63 in
Flange Outside Diameter Length	12.25 in
Length - Ground Shield	63.69 in
Length - Insulation Above Flange	26.75 in
Length - Insulation Below Flange	15.87 in
Length - Live Part Bottom	9.42 in
Length - Live Part Top	4.21 in
Length - Minimum Oil Immersion Level	3.62 in
Sealing Surface Inside Diameter	26.75 in
Sealing Surface Outside Diameter	4.37 in
Weight	10.25 in
	99 lb

Electrical Ratings

BIL	250 kV
Current Rating	1200 A
Minimum Creepage	35.80 in
Minimum Strike	18.20 in
Withstand Voltage - 60 Hz Dry	105 kV
kV Class	46 kV

Certifications and Compliance

Product Assets

Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites
Literature - Apparatus Bushings Selection Guide (TD02026E)
Literature - SDC™ GSU Bushings - Electro Composites (SF02018E)
Literature - SDC™ HV Generator Bushings - Electro Composites (SF02019E)
Literature - SDC™ HV Bushings - Electro Composites (SF02017E)
Literature - EC SDC Solid Dielectric Bushings v3
Literature - FRENCH V2 - EC Generation Bushings
Literature - FRENCH V2 - EC GSU Bushings
Literature - How an SDC Bushing Test Tap is Constructed
Sales Drawings - 479-00_5730-5395
Video - ElectroComposites Factory Tour: St. Jerome (VI00124E)



A proud member of the Hubbell Family.