

SDC™ Composite Bushing - 46KV

By Electro Composites
Catalog # 250-030-T-905-00

SDC™ 46kV-3000A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 21.0" Min.Oil Immersion Level/CT Pocket, 55.6" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-15NA High Temperature Cycloaliphatic Epoxy Compound for high temperature applications
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

Application

Transformer

General

Bottom Terminal Type	2-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-15NA - High Temp Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	2-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	26 in
Below Flange Length	33.50 in
Diameter - Above Flange Maximum	10.13 in
Diameter - Below Flange Maximum D <gt;/> 1"	5.02 in
Diameter - Below Flange Maximum P	5.02 in
Diameter - Live Part Bottom	2.50 in
Diameter - Live Part Top	4.00 in
Effective Length - Bottom Terminal	2.50 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	9.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter Length	11.00 in
Length - Drawlead Above Flange	59.50 in
Length - Ground Shield	21.00 in
Length - Insulation Above Flange	18.30 in
Length - Insulation Below Flange	29.80 in
Length - Live Part Bottom	3.70 in
Length - Live Part Top	3.80 in
Length - Minimum Oil Immersion Level	21.00 in
Sealing Surface Inside Diameter	5.11 in
Sealing Surface Outside Diameter	8.37 in
Top Terminal Min. Thread Length	2.50 in
Weight	168 lb

Electrical Ratings

BIL	250 kV
Current Rating	3000 A
Minimum Creepage	55.6 in
Minimum Creepage - Inside	NA
Minimum Strike	21.1 in

Minimum Strike - Inside	NA
Withstand Voltage - 60 Hz Dry	105 kV
kV Class	46 kV

Certifications and Compliance

Industry Standard(s) IEEE C57.19.01

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
[Literature - Apparatus Bushings Selection Guide \(TD02026E\)](#)
[Literature - SDC™ GSU Bushings - Electro Composites \(SF02018E\)](#)
[Literature - SDC™ HV Generator Bushings - Electro Composites \(SF02019E\)](#)
[Literature - SDC™ HV Bushings - Electro Composites \(SF02017E\)](#)
[Literature - EC SDC Solid Dielectric Bushings v3](#)
[Literature - FRENCH V2 - EC Generation Bushings](#)
[Literature - FRENCH V2 - EC GSU Bushings](#)
[Literature - How an SDC Bushing Test Tap is Constructed](#)
[Sales Drawings - SDC Bushing 46kV, 3000A Model: 250-030-T-905-00 \(S-9802-8736\)](#)
[Video - ElectroComposites Factory Tour: St. Jerome \(V100124E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
EC-250-030-T-905-00-SPEC-EN | REV 1/2024