

SDC™ Composite Bushing - 44kV

By Electro Composites
Catalog # 250-020-T-490-00

SDC™ 44kV-2000 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEC 60137, Bottom Connected for Air-to-Oil Applications, 4.6" Min. Oil Immersion Level/Ground Shield Length, 44.37" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- Meets IEC 60137 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

Application

Transformer

General

Bottom Terminal Type	1 1/2-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Bolt Holes - Top Terminal	4
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	Silver
Top Terminal Type	1X BLADE WITH 4X 0.56 DIA HOLES
Type	Condenser Bushings

Dimensions

Above Flange Length	24.88 in
Below Flange Length	15 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	4.15 in
Diameter - Below Flange Maximum P	4.37 in
Diameter - Live Part Bottom	2.00 in
Diameter - Live Part Top	3.50 in
Effective Length - Bottom Terminal	4.00 in
Effective Length - Top Terminal	3.38 in
Flange Mounting Hole Bolt Circle	9.75 in
Flange Mounting Hole Diameter	0.75 in
Flange Outside Diameter	11.38 in
Length	39.88 in
Length - Ground Shield	4.60 in
Length - Insulation Above Flange	15.82 in
Length - Insulation Below Flange	4.40 in
Length - Live Part Bottom	6.00 in
Length - Live Part Top	5.73 in
Length - Minimum Oil Immersion Level	4.60 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	9.00 in
Weight	74 lb

Electrical Ratings

BIL	250 kV
Current Rating	2000 A
Minimum Creepage	44.37 in
Minimum Strike	17.90 in
Withstand Voltage - 60 Hz Dry	95 kV
kV Class	44 kV

Certifications and Compliance

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
[Literature - Apparatus Bushings Selection Guide \(TDO2026E\)](#)
[Literature - SDC™ GSU Bushings - Electro Composites \(SF02018E\)](#)
[Literature - SDC™ HV Generator Bushings - Electro Composites \(SF02019E\)](#)
[Literature - SDC™ HV Bushings - Electro Composites \(SF02017E\)](#)
[Literature - EC SDC Solid Dielectric Bushings v3](#)
[Literature - FRENCH V2 - EC Generation Bushings](#)
[Literature - FRENCH V2 - EC GSU Bushings](#)
[Literature - How an SDC Bushing Test Tap is Constructed](#)
[Sales Drawings - 490-00_5832-5507](#)
[Video - ElectroComposites Factory Tour: St. Jerome \(VI00124E\)](#)



A proud member of the Hubbell Family.