

# HUBBELL

## Power Systems

### SDC™ Composite Bushing - 52kV

By Electro Composites  
 Catalog # [250-006-T-454-00](#)

SDC™ 52kV-630DL A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEC 60137, Drawlead Connected for Air-to-Oil Applications, 5.9" Min. Oil Immersion Level/CT Pocket Length, 51.9" Min. Creepage Length



#### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEC 60137 Electrical and Mechanical Requirements

#### General

Application	Transformer
Bottom Terminal Type	None
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	8
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1.180 DIA SMOOTH
Type	SDC - Solid Dielectric Capacitor

#### Dimensions

Above Flange Length	30.2 in
Below Flange Length	12.88 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D > 1"	4.15 in
Diameter - Below Flange Maximum P	4.15 in
Diameter - Live Part Bottom	1.25 in
Diameter - Live Part Top	3.50 in
Dimensions	43.05 in x 11.42 in x 11.42 in
Effective Length - Top Terminal	3.13 in
Flange Mounting Hole Bolt Circle	9.72 in
Flange Mounting Hole Diameter	0.69 in
Flange Outside Diameter	11.42 in
Height	11.42 in
Length	43.05 in
Length - Drawlead Above Flange	26.00 in
Length - Ground Shield	5.90 in
Length - Insulation Above Flange	20.40 in
Length - Insulation Below Flange	6.18 in
Length - Live Part Bottom	0.80 in
Length - Live Part Top	5.90 in
Length - Minimum Oil Immersion Level	5.90 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	9.03 in
Stud Inside Diameter	1 in
Thread Size - Drawlead Connector	3/4-12
Weight	55 lb
Width	11.42 in

## Electrical Ratings

BIL	250 kV
Current Rating	630 A
Minimum Creepage	51.9 in
Minimum Strike	22.6 in
Withstand Voltage - 60 Hz Dry	95 kV
kV Class	52 kV

## Certifications And Compliance

Industry Standard(s)	IEC 60137
----------------------	-----------

## Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 454-00\\_5569-5241](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
EC-250006T45400-SPEC-EN | REV 6/2024