

HUBBELL

Power Systems

SDC™ Composite Bushing - 46kV

By Electro Composites
 Catalog # [250-004-T-296-01](#)

SDC™ 46kV-400DL A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Drawlead Connected for Air-to-Oil Applications, 16.5" Min. Oil Immersion Level/CT Pocket Length, 49.6" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements

General

Application	Transformer
Bottom Terminal Type	None
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1 1/8-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	29.91 in
Below Flange Length	27 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	3.48 in
Diameter - Below Flange Maximum P	3.48 in
Diameter - Live Part Bottom	1.25 in
Diameter - Live Part Top	3.00 in
Dimensions	56.91 in x 10.00 in x 10.00 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	8.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	10 in
Height	10 in
Length	56.91 in
Length - Drawlead Above Flange	26.35 in
Length - Ground Shield	16.50 in
Length - Insulation Above Flange	20.40 in
Length - Insulation Below Flange	9.90 in
Length - Live Part Bottom	0.60 in
Length - Live Part Top	4.90 in
Length - Minimum Oil Immersion Level	16.50 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	7.37 in
Stud Inside Diameter	1 in
Thread Size - Drawlead Connector	3/4-12
Top Terminal Min. Thread Length	2.5 in
Weight	57 lb
Width	10 in

Electrical Ratings

BIL	250 kV
Current Rating	400 A
Minimum Creepage	49.6 in
Minimum Strike	22.6 in
Withstand Voltage - 60 Hz Dry	105 kV
kV Class	46 kV

Certifications And Compliance

Industry Standard(s) IEEE C57.19.01

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 296-01_4904-4641](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
EC-250004T29601-SPEC-EN | REV 6/2024