

HUBBELL

Power Systems

SDC™ Composite Bushing - 46kV

By Electro Composites
 Catalog # [250-012-B-081-00](#)

SDC™ 46kV-1200 A OCB Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE/IEC, Bottom Connected for Air-to-Oil Applications, 20" Min. Oil Immersion Level/CT Pocket Length, 38.3" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Tested to C57.19.01/IEC 60137

General

Application	OCB
Bottom Terminal Type	1 1/2-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	28.37 in
Below Flange Length	33.5 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D > 1"	3.74 in
Diameter - Below Flange Maximum P	3.74 in
Diameter - Live Part Bottom	1.50 in
Diameter - Live Part Top	3.00 in
Dimensions	61.87 in x 9.63 in x 9.63 in
Effective Length - Bottom Terminal	2.38 in
Effective Length - Top Terminal	4.00 in
Flange Mounting Hole Bolt Circle	8.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	9.63 in
Height	9.63 in
Length	61.87 in
Length - Ground Shield	20.00 in
Length - Insulation Above Flange	18.20 in
Length - Insulation Below Flange	10.50 in
Length - Live Part Bottom	3.00 in
Length - Live Part Top	5.30 in
Length - Minimum Oil Immersion Level	20.00 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	7.37 in
Top Terminal Min. Thread Length	4 in
Weight	89 lb
Width	9.63 in

Electrical Ratings

BIL	250 kV
Current Rating	1200 A
Minimum Creepage	38.3 in
Minimum Strike	20.5 in
Withstand Voltage - 60 Hz Dry	105 kV
kV Class	46 kV

Certifications And Compliance

Industry Standard(s) IEEE/IEC

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 081-00_2256-1398](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
EC-250012B08100-SPEC-EN | REV 6/2024