

SDC™ Composite Bushing - 46kV

By Electro Composites
Catalog # 250-012-T-081-02

SDC™ 46kV-1200 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEC 60137, Bottom Connected for Air-to-Oil Applications, 20" Min. Oil Immersion Level/CT Pocket Length, 38" Min. Creepage Length

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEC 60137 Electrical and Mechanical Requirements

Application

Transformer

General

Bottom Terminal Type	1 1/2-12
Catalog Number	250-012-T-081-02
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	Tin
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	28.37 in
Below Flange Length	33.5 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt; 1"	3.74 in
Diameter - Below Flange Maximum P	3.74 in
Diameter - Conductor Outside Under Insulation	1.5 in
Diameter - Live Part Bottom	1.50 in



*Representative Image

Diameter - Live Part Top	3.00 in
Diameter - Rod / Tube	1.5 in
Dimensions	61.87 in x 9.63 in x 9.63 in
Effective Length - Bottom Terminal	2.38 in
Effective Length - Top Terminal	4.00 in
Flange Mounting Hole Bolt Circle	8.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	9.63 in
Height	9.63 in
Length	61.87 in
Length - Ground Shield	20.00 in
Length - Insulated Section	53.6 in
Length - Insulation Above Flange	18.20 in
Length - Insulation Below Flange	10.50 in
Length - Live Part Bottom	3.00 in
Length - Live Part Top	5.30 in
Length - Minimum Oil Immersion Level	20.00 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	7.37 in
Thickness	1.12 in
Top Terminal Min. Thread Length	4 in
Weight	89 lb
Width	9.63 in

Electrical Ratings

BIL	250 kV
Current Rating	1200 A
Minimum Creepage	38 in
Minimum Strike	20.5 in
Withstand Voltage - 60 Hz Dry kV Class	105 kV
	46 kV

Certifications And Compliance

Industry Standard(s)	IEC 60137
----------------------	-----------

Product Assets

[Catalogs - Electro Composites SDC™ composite bushings](#)
[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
[Literature - SDC™ HV Generator Bushings - Electro Composites](#)
[Literature - How an SDC Bushing Test Tap is Constructed](#)
[Literature - TRAVERSÉE SDC™ ÉLECTRO COMPOSITES DE TYPE GSU](#)
[Literature - SDC™ GSU Bushings - Electro Composites](#)

[Literature - TRAVERSÉE SDC™ ÉLECTRO COMPOSITES POUR GÉNÉRATEUR](#)
[Literature - Apparatus Bushings Selection Guide](#)
[Literature - ÉLECTRO COMPOSITES TRAVERSÉE HAUTE TENSION SDC™](#)
[Literature - SDC™ HV Bushings - Electro Composites](#)
[Sales Drawings - 081-02_5780-5392](#)
[Specifications - 250012T08102](#)
[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
EC-250012T08102-SPEC-EN | REV 3/2025