

SDC™ Composite Bushing - 69kV

By Electro Composites
Catalog # 350-004-T-712-01

SDC™ 69kV-400DL A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Drawlead Connected for Air-to-Oil Applications, 11.3" Min. Oil Immersion Level/CT Pocket Length, 65.8" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

Application

Transformer

General

Bottom Terminal Type	None
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	Silver
Top Terminal Type	1 1/8-12
Type	Condenser Bushings

Dimensions

Above Flange Length	36.6 in
Below Flange Length	23 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	5.02 in
Diameter - Below Flange Maximum P	5.02 in
Diameter - Live Part Bottom	1.25 in
Diameter - Live Part Top	3.50 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	10.88 in
Flange Mounting Hole Diameter	0.63 in
Flange Outside Diameter	12.00 in
Length	59.60 in
Length - Drawlead Above Flange	33.00 in
Length - Ground Shield	11.30 in
Length - Insulation Above Flange	27.30 in
Length - Insulation Below Flange	10.70 in
Length - Live Part Bottom	1.00 in
Length - Live Part Top	5.50 in
Length - Minimum Oil Immersion Level	11.30 in
Sealing Surface Inside Diameter	5.11 in
Sealing Surface Outside Diameter	10.00 in
Stud Inside Diameter	1.00 in
Thread Size - Drawlead Connector	3/4-12
Top Terminal Min. Thread Length	2.50 in
Weight	84 lb

Electrical Ratings

BIL	350 kV
Current Rating	400 A
Minimum Creepage	65.80 in
Minimum Strike	29.30 in

Withstand Voltage - 60 Hz 160 kV
Dry
kV Class 69 kV

Certifications and Compliance

Industry Standard(s) IEEE C57.19.01

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
[Literature - Apparatus Bushings Selection Guide \(TD02026E\)](#)
[Literature - SDC™ GSU Bushings - Electro Composites \(SF02018E\)](#)
[Literature - SDC™ HV Generator Bushings - Electro Composites \(SF02019E\)](#)
[Literature - SDC™ HV Bushings - Electro Composites \(SF02017E\)](#)
[Literature - EC SDC Solid Dielectric Bushings v3](#)
[Literature - FRENCH V2 - EC Generation Bushings](#)
[Literature - FRENCH V2 - EC GSU Bushings](#)
[Literature - How an SDC Bushing Test Tap is Constructed](#)
[Sales Drawings - 712-01_8316-7712](#)
[Video - ElectroComposites Factory Tour: St. Jerome \(V100124E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
EC-350-004-T-712-01-SPEC-EN | REV 1/2024