

## SDC™ Composite Bushing - 69 kV

By Electro Composites  
Catalog # 350-412-T-1030-00

SDC™ 69kV-400/1200A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom-Drawlead Connected for Air-to-Oil Applications, 21.0" Min.Oil Immersion Level/CT Pocket, 138.9" Min. Creepage Length



\*Representative Image

### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

### Application

Transformer

### General

Bottom Terminal Type	1 1/2-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	Silver
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

### Dimensions

Above Flange Length	51 in
Below Flange Length	37.5 in
Diameter - Above Flange Maximum	11.13 in
Diameter - Below Flange Maximum D <gt;/> 1"	5.02 in
Diameter - Below Flange Maximum P	5.02 in
Diameter - Live Part Bottom	1.50 in
Diameter - Live Part Top	3.50 in
Effective Length - Bottom Terminal	2.50 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	9.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter Length	11.00 in
Length - Drawlead Above Flange	88.50 in
Length - Ground Shield	47.00 in
Length - Insulation Above Flange	21.00 in
Length - Insulation Below Flange	41.50 in
Length - Live Part Bottom	12.7 in
Length - Live Part Top	3.8 in
Length - Minimum Oil Immersion Level	5.8 in
Sealing Surface Inside Diameter	21.00 in
Sealing Surface Outside Diameter	5.11 in
Stud Inside Diameter	8.37 in
Thread Size - Drawlead Connector	0.88 in
Top Terminal Min. Thread Length	3/4-12
Weight	2.50 in
	197 lb

### Electrical Ratings

BIL	350 kV
Current Rating	400/1200 A

Minimum Creepage	138.9 in
Minimum Strike	45.5 in
Withstand Voltage - 60 Hz Dry	160 kV
kV Class	69 kV

## Certifications and Compliance

Industry Standard(s) IEEE C57.19.01

## Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)  
[Literature - Apparatus Bushings Selection Guide \(TD02026E\)](#)  
[Literature - SDC™ GSU Bushings - Electro Composites \(SF02018E\)](#)  
[Literature - SDC™ HV Generator Bushings - Electro Composites \(SF02019E\)](#)  
[Literature - SDC™ HV Bushings - Electro Composites \(SF02017E\)](#)  
[Literature - EC SDC Solid Dielectric Bushings v3](#)  
[Literature - FRENCH V2 - EC Generation Bushings](#)  
[Literature - FRENCH V2 - EC GSU Bushings](#)  
[Literature - How an SDC Bushing Test Tap is Constructed](#)  
[Sales Drawings - 1030-00\\_7864-9736](#)  
[Video - ElectroComposites Factory Tour: St. Jerome \(VI00124E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
EC-350-412-T-1030-00-SPEC-EN | REV 1/2024