

# HUBBELL

## Power Systems

### SDC™ Composite Bushing - 72.5kV

By Electro Composites  
 Catalog # [325-004-T-495-00](#)

SDC™ 72.5kV-400DL A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEC 60137, Drawlead Connected for Air-to-Oil Applications, 10" Min. Oil Immersion Level/CT Pocket Length, 59.1" Min. Creepage Length



\*Representative Image

#### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEC 60137 Electrical and Mechanical Requirements

#### General

Application	Transformer
Bottom Terminal Type	None
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

#### Dimensions

Above Flange Length	36.31 in
Below Flange Length	20.25 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	4.15 in
Diameter - Below Flange Maximum P	4.37 in
Diameter - Live Part Bottom	1.25 in
Diameter - Live Part Top	3.50 in
Dimensions	56.56 in x 12.50 in x 12.50 in
Effective Length - Top Terminal	4.00 in
Flange Mounting Hole Bolt Circle	10.88 in
Flange Mounting Hole Diameter	0.63 in
Flange Outside Diameter	12.5 in
Height	12.5 in
Length	56.56 in
Length - Drawlead Above Flange	31.25 in
Length - Ground Shield	10.00 in
Length - Insulation Above Flange	25.00 in
Length - Insulation Below Flange	9.65 in
Length - Live Part Bottom	0.60 in
Length - Live Part Top	8.00 in
Length - Minimum Oil Immersion Level	10.00 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	10.25 in
Stud Inside Diameter	1 in
Thread Size - Drawlead Connector	3/4-10
Top Terminal Min. Thread Length	4 in
Weight	67 lb
Width	12.5 in

## Electrical Ratings

BIL	350 kV
Current Rating	400 A
Minimum Creepage	59.1 in
Minimum Strike	27.1 in
Withstand Voltage - 60 Hz Dry	140 kV
kV Class	72.5 kV

## Certifications And Compliance

Industry Standard(s) IEC 60137

## Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 495-00\\_5859-5467](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
EC-325004T49500-SPEC-EN | REV 6/2024