

## SDC™ Composite Bushing - 72.5kV

By Electro Composites  
Catalog # 350-004-T-466-01

SDC™ 72.5kV-400DL A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per CSA C88.1, Drawlead Connected for Air-to-Oil Applications, 15" Min. Oil Immersion Level/CT Pocket Length, 59.1" Min. Creepage Length



\*Representative Image

### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- Meets CSA C88.1 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

### Application

Transformer

### General

Bottom Terminal Type	None
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1 1/2-12
Type	Condenser Bushings

### Dimensions

Above Flange Length	33.06 in
Below Flange Length	26.75 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	4.15 in
Diameter - Below Flange Maximum P	4.29 in
Diameter - Live Part Bottom	1.25 in
Diameter - Live Part Top	3.50 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	8.25 in
Flange Mounting Hole Diameter	0.75 in
Flange Outside Diameter	9.50 in
Length	59.81 in
Length - Drawlead Above Flange	29.50 in
Length - Ground Shield	15.00 in
Length - Insulation Above Flange	25.00 in
Length - Insulation Below Flange	10.95 in
Length - Live Part Bottom	0.80 in
Length - Live Part Top	4.60 in
Length - Minimum Oil Immersion Level	15.00 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	7.50 in
Stud Inside Diameter	1.00 in
Thread Size - Drawlead Connector	3/4-10
Top Terminal Min. Thread Length	2.50 in
Weight	68 lb

### Electrical Ratings

BIL	350 kV
Current Rating	400 A
Minimum Creepage	59.10 in
Minimum Strike	2710 in

Withstand Voltage - 60 Hz 175 kV  
Dry  
kV Class 72.5 kV

### **Certifications and Compliance**

Industry Standard(s) CSA C88.1

### **Product Assets**

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)  
[Literature - Apparatus Bushings Selection Guide \(TD02026E\)](#)  
[Literature - SDC™ GSU Bushings - Electro Composites \(SF02018E\)](#)  
[Literature - SDC™ HV Generator Bushings - Electro Composites \(SF02019E\)](#)  
[Literature - SDC™ HV Bushings - Electro Composites \(SF02017E\)](#)  
[Literature - EC SDC Solid Dielectric Bushings v3](#)  
[Literature - FRENCH V2 - EC Generation Bushings](#)  
[Literature - FRENCH V2 - EC GSU Bushings](#)  
[Literature - How an SDC Bushing Test Tap is Constructed](#)  
[Sales Drawings - 466-01\\_5596-8244](#)  
[Video - ElectroComposites Factory Tour: St. Jerome \(VIO0124E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
EC-350-004-T-466-01-SPEC-EN | REV 1/2024