

## SDC™ Composite Bushing - 72.5kV

By Electro Composites  
Catalog # 350-012-B-350-02

SDC™ 72.5kV-1200 A OCB Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per CSA C88.1, Bottom Connected for Air-to-Oil Applications, 20" Min. Oil Immersion Level/CT Pocket Length, 80.2" Min. Creepage Length



\*Representative Image

### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- Meets CSA C88.1 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

### Application

OCB

### General

Bottom Terminal Type	1 1/2-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

### Dimensions

Above Flange Length	38.60 in
Below Flange Length	46.75 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	4.15 in
Diameter - Below Flange Maximum P	4.29 in
Diameter - Live Part Bottom	1.50 in
Diameter - Live Part Top	3.00 in
Dimensions	84.38 in x 11.00 in x 11.00 in
Effective Length - Bottom Terminal	2.75 in
Effective Length - Top Terminal	2.75 in
Flange Mounting Hole Bolt Circle	9.50 in
Flange Mounting Hole Diameter	0.75 in
Flange Outside Diameter	11.00 in
Height	11.00 in
Length	84.38 in
Length - Ground Shield	20.00 in
Length - Insulation Above Flange	29.70 in
Length - Insulation Below Flange	21.95 in
Length - Live Part Bottom	4.80 in
Length - Live Part Top	5.50 in
Length - Minimum Oil Immersion Level	20.00 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	8.75 in
Top Terminal Min. Thread Length	2.75 in
Weight	131 lb
Width	11.00 in

### Electrical Ratings

BIL	350 kV
Current Rating	1200 A
Minimum Creepage	80.20 in
Minimum Strike	32.00 in

Minimum Strike	52.00 in
Withstand Voltage - 60 Hz Dry	175 kV
kV Class	72.5 kV

## Certifications and Compliance

Industry Standard(s)                      CSA C88.1

## Product Assets

[Catalogs - Electro Composites SDC Bushings](#)  
[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)  
[Literature - Apparatus Bushings Selection Guide \(TD02026E\)](#)  
[Literature - SDC™ GSU Bushings - Electro Composites \(SF02018E\)](#)  
[Literature - SDC™ HV Generator Bushings - Electro Composites \(SF02019E\)](#)  
[Literature - SDC™ HV Bushings - Electro Composites \(SF02017E\)](#)  
[Literature - EC SDC Solid Dielectric Bushings v3](#)  
[Literature - FRENCH V2 - EC Generation Bushings](#)  
[Literature - FRENCH V2 - EC GSU Bushings](#)  
[Literature - How an SDC Bushing Test Tap is Constructed](#)  
[Sales Drawings - 350-02\\_6182-5774](#)  
[Video - ElectroComposites Factory Tour: St. Jerome \(V100124E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
EC-350-012-B-350-02-SPEC-EN | REV 1/2024