

HUBBELL

Power Systems

SDC™ Composite Bushing - 69kV

By Electro Composites
 Catalog # [350-004-T-386-05](#)

SDC™ 69kV-400DL A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Drawlead Connected for Air-to-Oil Applications, 21" Min. Oil Immersion Level/CT Pocket Length, 66.2" Min. Creepage Length



Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements

General

Application	Transformer
Bottom Terminal Type	None
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1 1/8-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	36.56 in
Below Flange Length	35 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D > 1"	4.15 in
Diameter - Below Flange Maximum P	4.34 in
Diameter - Live Part Bottom	1.50 in
Diameter - Live Part Top	3.50 in
Dimensions	71.56 in x 10.63 in x 10.63 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	9.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	10.63 in
Height	10.63 in
Length	71.56 in
Length - Drawlead Above Flange	33.00 in
Length - Ground Shield	21.00 in
Length - Insulation Above Flange	27.70 in
Length - Insulation Below Flange	13.00 in
Length - Live Part Bottom	1.00 in
Length - Live Part Top	5.80 in
Length - Minimum Oil Immersion Level	21.00 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	8.37 in
Stud Inside Diameter	1.25 in
Thread Size - Drawlead Connector	3/4-12
Top Terminal Min. Thread Length	2.5 in
Weight	76 lb
Width	10.63 in

Electrical Ratings

BIL	350 kV
Current Rating	400 A
Minimum Creepage	66.2 in
Minimum Strike	29.5 in
Withstand Voltage - 60 Hz Dry	160 kV
kV Class	69 kV

Certifications And Compliance

Industry Standard(s) IEEE C57.19.01

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 386-05_7860-7524](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
EC-350004T38605-SPEC-EN | REV 6/2024