

# HUBBELL

## Power Systems

### SDC™ Composite Bushing - 72.5kV

By Electro Composites  
 Catalog # [350-012-B-339-05](#)

SDC™ 72.5kV-1200 A OCB Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per CSA C88.1, Bottom Connected for Air-to-Oil Applications, 16.5" Min. Oil Immersion Level/CT Pocket Length, 80.2" Min. Creepage Length



\*Representative Image

#### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets CSA C88.1 Electrical and Mechanical Requirements

#### General

Application	OCB
Bottom Terminal Type	1 1/2-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

#### Dimensions

Above Flange Length	36.75 in
Below Flange Length	33.5 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	4.15 in
Diameter - Below Flange Maximum P	4.28 in
Diameter - Live Part Bottom	1.50 in
Diameter - Live Part Top	3.00 in
Dimensions	70.25 in x 9.75 in x 9.75 in
Effective Length - Bottom Terminal	2.25 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	8.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	9.75 in
Height	9.75 in
Length	70.25 in
Length - Ground Shield	16.50 in
Length - Insulation Above Flange	29.70 in
Length - Insulation Below Flange	13.80 in
Length - Live Part Bottom	3.20 in
Length - Live Part Top	3.60 in
Length - Minimum Oil Immersion Level	16.50 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	7.37 in
Top Terminal Min. Thread Length	2.5 in
Weight	112 lb
Width	9.75 in

## Electrical Ratings

BIL	350 kV
Current Rating	1200 A
Minimum Creepage	80.2 in
Minimum Strike	32.1 in
Withstand Voltage - 60 Hz Dry	175 kV
kV Class	72.5 kV

## Certifications And Compliance

Industry Standard(s)                      CSA C88.1

## Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 339-05\\_1543-9234](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
EC-350012B33905-SPEC-EN | REV 6/2024