

Compression Splice Conventional (Hex Die) Jumper Loop-Partial Tension

By FARGO
Catalog # 40110



*Representative Image

"Compression Splice, Conventional 2-Die, Jumper Loop, for AAC, AAAC, ACAR, ACSR, SAC Dia. Range: 1.729"-1.762", COMP/TW Dia. Range: 1.545"-1.608"

General

Aluminum Die	30AH
Compression Method	Conventional
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Aluminum Alloy
Press Minimum	60 to
UPC	096359250654

Dimensions

Length Before Compression	9.2 in
Messenger Diameter Range	0 - 0
Weight	1.568 lb

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Conductor Compatibility	ACSR-Stilt-715.5-24/7;ACSR-Starling-715.5-26/7;ACSR-Coot-795-36/1;AAC-Arbutus-795-37;AAC-Lilac-795-61
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	1.051 in
Conductor Diameter - Minimum	1.026 in
Conductor Diameter Range	1.026 - 1.051

Certifications and Compliance

UL Listed	No
-----------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)