

HUBBELL

Power Systems

Compression Splice Conventional (Hex Die) Jumper Loop-Minimum Tension

By FARGO
Catalog # 40117



*Representative Image

"Conventional (Two Die) Compression Jumper Loop Splice available for ACSR and AAC conductor. Loop Splice is Minimum Tension connector (no steel component required)."

Features

- "SAC Diameter Range: 1.014"-1.108"
- COMP/TW Diameter Range: 0.927"-1.010"
- PC suffix denotes prefilled Joint Compound
- Material: Extruded Aluminum Tube.
- Die Size: 30AH 60 Ton Press Min."

General

Aluminum Die	30AH
Compression Method	Conventional
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Aluminum Alloy
Press Minimum	60 to
Tension Range	0 lb
UPC	096359250678

Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	9.7 in
Messenger Diameter Range	0 - 0
Weight	1.793 lb

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Conductor Compatibility	ACSR-Cuckoo-795-24/7;ACSR-Drake-795-26/7;ACSR-Condor-795-54/7;AAC-Cockscomb-900-37;AAC-Snapdragon-900-61
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	1.108 in
Conductor Diameter - Minimum	1.092 in
Conductor Diameter Range	1.092 - 1.108
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Certifications And Compliance

UL Listed	No
-----------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-40117-SPEC-EN | REV 6/2024