


# HUBBELL Power Systems

## Compression Splice Conventional (Hex Die) Jumper Loop-Minimum Tension

By FARGO  
Catalog # [40609](#)



\*Representative Image

"Conventional (Two Die) Compression Jumper Loop Splice available for ACSR and AAC conductor. Loop Splice is Minimum Tension connector (no steel component required).".

### Features

- "SAC Diameter Range: 0.563"-0.590"
- PC suffix denotes prefilled Joint Compound
- Material: Extruded Aluminum Tube.
- Die Size: 75AH 12 Ton Press Min."

### General

Aluminum Die	75AH
Compression Method	Conventional
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Aluminum Alloy
Press Minimum	12 to
Tension Range	0 lb
UPC	096359250777

### Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	5.3 in
Messenger Diameter Range	0 - 0
Weight	0.137 lb

### Electrical Ratings

Voltage Application	Standard
---------------------	----------

### Conductor Related

Conductor Compatibility	ACSR-Penguin-4/0-6/1;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAAC 6201 Alloy-Alliance-246.9-6/18
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	0.593 in
Conductor Diameter - Minimum	0.563 in
Conductor Diameter Range	0.563 - 0.593
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

### Certifications And Compliance

UL Listed	No
-----------	----

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
FG-40609-SPEC-EN | REV 6/2024