

Vibration Damper, Stockbridge

By FARGO
Catalog # 6071513



Features

-
-
-
-
-
-

General

Bolt Installation Torque (Recommended)	25 ft-lbs
Catalog Number	6071513
Material - Clamp	Aluminum
Material - Hardware	Aluminum
Style	4R Stockbridge Damper
UPC	096359251958

Dimensions

Clamping - Maximum	1.425 in
Clamping - Minimum	1.131 in
Diameter - Bolt	0.5 in
Dimensions	8.86 in x 3.84 in x 4.06 in
Height	4.06 in
Length	8.86 in
Weight	15.7 lb
Width	3.84 in

Electrical Ratings

Voltage Application	Standard Voltage/EHV
---------------------	----------------------

Conductor Related

Clamping Range	1.131- 1.425
Conductor Compatibility	ACSR-Mallard-795-30/19;ACSR-Ruddy-900-

45/7;ACSR-Canary-900-54/7;ACSR-Rail-954-45/7;ACSR-Cardinal-954-54/7;ACSR-Ortolan-1033.5-45/7;ACSR-Curlew-1033.5-54/7;ACSR-Bluejay-1113-45/7;ACSR-Finch-1113-54/19;ACSR-Bunting-1192.5-45/7;ACSR-Grackle-1192.5-54/19;ACSR-Bittern-1272-45/7;ACSR-Pheasant-1272-54/19;ACSR-Dipper-1351.5-45/7;ACSR-Martin-1351.5-54/19;AAC-Camellia-1000-61;AAC-Bluebell-1033.5-37;AAC-Larkspur-1033.5-61;AAC-Marigold-1113-61;AAC-Hawthorn-1192.5-61;AAC-Narcissus-1272-61;AAC-Columbine-1351.5-61;AAC-Carnation-1431-61;AAC-Gladiolus-1510.5-61;ACAR-1024.5-30/7;ACAR-1109-30/7;ACAR-1172-30/7;ACAR-1172-18/19

Conductor Diameter (Main) - Maximum 0 in

Logistics

Pallet Quantity	60
-----------------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)
[Sales Drawings - 60715-13_S6159B \(1\)](#)
[Specifications - 6071513](#)