


Vibration Damper

By FARGO
Catalog # [6072025](#)

"Y-Clevis Eye, Bent Bolt Diameter-0.750", Clevis Eye Width-1.000", Hole Diameter-0.688", UTS 30,000 lb"



*Representative Image

Features

- "4-R vibration dampers effectively prevent fatigue damage to conductor and static wires caused by wind-induced aeolian vibration
- To specify Torque Head/Break Away bolt option, add suffix "O" to catalog number"

General

Bolt Installation Torque (Recommended)	40 ft-lbs
Material - Clamp	Aluminum
Material - Hardware	Aluminum
Style	4R Stockbridge Damper
UPC	096359511373

Dimensions

Clamping - Maximum	2.560 in
Clamping - Minimum	1.94 in
Diameter - Bolt	0.5 in
Weight	22.5 lb

Electrical Ratings

Voltage Application	Standard Voltage/EHV
---------------------	----------------------

Conductor Related

Clamping Range	1.94- 2.560
----------------	-------------

Logistics

Pallet Quantity	48
-----------------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)