

Compression Splice - Full Tension

By FARGO
Catalog # 811222

Full Tension Compression Splice for Alumoweld® and EHS Steel.



*Representative Image

Features

- Shield Wire Outside Diameter - 0.306 - 0.313 inches
- For use with 5/16 EHS Steel or 7 #10, 3 #7 Alumoweld®
- Material: Body - aluminum alloy
- Die Size 12SH 60 Ton Press Minimum
- Add "PC" for factory loaded inhibitor
- For extra length repair splice add "XL" suffix and repair cutoff Length in Inches. Example: 811425XL24

General

Catalog Number	811222
Compression Method	Single Die
EU RoHS Indicator	No
Material	Aluminum Alloy
Press Minimum	60 to
Tension Range	0 lb
UPC	096359251613

Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	8 in

Messenger Diameter Range	0 - 0
Weight	0.294 lb

Conductor Related

Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	0.313 in
Conductor Diameter - Minimum	0.306 in
Conductor Diameter Range	0.306 - 0.313
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
UL Listed	No

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Specifications - 811222](#)