

Compression Splice - Full Tension

By FARGO
Catalog # [811425](#)

Full Tension Compression Splice for Alumoweld® and EHS Steel.



*Representative Image

Features

- Shield Wire Outside Diameter - 0.343 - 0.375 inches
- For use with 3/8 EHS Steel or 7 #9, 3 #6 Alumoweld®
- Material: Body - aluminum alloy
- Die Size 14SH 60 Ton Press Minimum
- Add "PC" for factory loaded inhibitor
- For extra length repair splice add "XL" suffix and repair cutoff Length in Inches. Example: 811425XL24

General

| | |
|--------------------|----------------|
| Compression Method | Single Die |
| Material | Aluminum Alloy |
| Press Minimum | 60 to |
| Tension Range | 0 lb |
| UPC | 096359251620 |

Dimensions

| | |
|------------------------------------|------------------------------|
| Adjustment Step | 0 in |
| Assembly Rating (Ultimate) | 0 lb |
| Dimensions | 9.89 in x 0.875 in x 0.75 in |
| Height | 0.75 in |
| Insulator / Conductor Hole Spacing | 0 in |
| Length | 9.89 in |
| Length Before Compression | 9.9 in |
| Messenger Diameter Range | 0 - 0 |
| Weight | 0.49 lb |
| Width | 0.875 in |

Conductor Related

| | |
|-------------------------------------|---------------|
| Conductor Diameter (Main) - Maximum | 0 in |
| Conductor Diameter (Main) - Minimum | 0 in |
| Conductor Diameter (Main) Range | 0 - 0 |
| Conductor Diameter - Maximum | 0.375 in |
| Conductor Diameter - Minimum | 0.343 in |
| Conductor Diameter Range | 0.343 - 0.375 |
| Messenger Diameter - Maximum | 0 in |
| Messenger Diameter - Minimum | 0 in |

Certifications And Compliance

| | |
|-----------|----|
| UL Listed | No |
|-----------|----|

Logistics

| | |
|-----------------|------|
| Pallet Quantity | 2016 |
|-----------------|------|

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Sales Drawings - 811425 CUTSHEET](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-811425-SPEC-EN | REV 6/2024