

HUBBELL Power Systems

Compression Deadend, Uni-Grip®(One Die), Full Tension

By FARGO
Catalog # [A021245](#)

Full tension deadend assembly for ACSR conductors consists of a prefilled aluminum deadend body precompressed onto a steel eye, prefilled 15° jumper terminals, mounting hardware and core gripping unit.



*Representative Image

Features

- For use with 795.0 kcmil 26/7 ACSR code name Drake
- Full tension Deadend assembly
- Outside Diameter is 1.108 inches
- Double Tongue
- Steel eye factory compressed in vertical orientation
- One Die Compression with die size 12CD
- Material: Body - seamless extruded aluminum alloy tube, Eye - galvanized forged steel, Terminal - seamless extruded aluminum alloy tube, Hardware - aluminum alloy.
- Aluminum deadend body and jumper terminal are prefilled with joint compound
- Uni-Grip Deadends and Jumper Terminals for conductors 1" dia or larger are EHV rated
- Jumper Terminal and mounting hardware included as standard. To omit jumper terminal, add suffix "NT" to catalog number. Example: A0112451NT.
- To omit both jumper terminal and deadend tongue, add suffix "NPNT" to the catalog number. Example: A0112451NPNT.
- For XL repair deadend, add suffix "XL" and repair cutoff length in inches. Example: A0112451XL24.

General

| | |
|--|---------------------------------------|
| Bolt Installation Torque (Recommended) | 0 ft-lbs |
| Compression Method | Uni-Grip (single die system) |
| Die Size | 12CD |
| EU RoHS Indicator | No |
| Material | Aluminum; Steel |
| Material - Body | Seamless Extruded Aluminum Alloy |
| Material - Eye | Galvanized Forged Steel |
| Material - Hardware | Aluminum Alloy |
| Material - Terminal | Seamless Extruded Aluminum Alloy |
| Number of Bolt Holes | 4 |
| Number of Pad Holes | 0 |
| Press Minimum | 60 to |
| Product Category | Eye |
| Style | Uni-Grip, Single Tongue, Vertical Eye |
| Tension Range | 0 lb |
| Type | Compression |
| UPC | 096359276579 |

Dimensions

| | |
|------------------------------------|-----------|
| Actual Clamp Strand Diameter Range | 0 in |
| Adjustment Step | 0 in |
| Angle - Pad | 0 ° |
| Clamping - Maximum | 0 in |
| Clamping - Minimum | 0 in |
| Diameter - Clamping Hardware | 0 in |
| Diameter - Clevis Pin | 0 in |
| Diameter - Eye Hole | 0 in |
| Diameter - Inside | 0 in |
| Diameter - Outside | 1.108 in |
| Diameter - Pad Bolt | 0 in |
| Length - Pin | 0 in |
| Length Before Compression | 17.2 in |
| Messenger Diameter Range | 0 - 0 |
| Take Up | 0 in |
| Thickness - Pad | 0 in |
| Total Adjustment | 0 in |
| Weight | 11.103 lb |
| Width - Pad | 3 in |

Electrical Ratings

| | |
|---------------------|---------------|
| Voltage Application | EHV; Standard |
|---------------------|---------------|

Conductor Related

| | |
|-------------------------------------|---------------------|
| Clamping Range | 0- 0 |
| Conductor Compatibility | ACSR-Drake-795-26/7 |
| Conductor Diameter (Main) - Maximum | 0 in |
| Conductor Diameter (Main) - Minimum | 0 in |
| Conductor Diameter (Main) Range | 0 - 0 |
| Messenger Diameter - Maximum | 0 in |
| Messenger Diameter - Minimum | 0 in |

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-A021245-SPEC-EN | REV 6/2024