

# HUBBELL

## Power Systems

### Compression Deadend, Uni-Grip®(One Die), Full Tension

By FARGO

Catalog # [A031561NT](#)



\*Representative Image

#### Features

- 
- 

#### General

Bolt Installation Torque (Recommended)	0 ft-lbs
Compression Method	Uni-Grip (single die system)
Die Size	15CD
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Number of Bolt Holes	4
Number of Pad Holes	0
Press Minimum	60 to
Product Category	Eye
Style	Uni-Grip, Single Tongue, Horizontal Eye
Tension Range	0 lb
Terminal Option	No
Type	Compression

#### Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0 °
Clamping - Maximum	0 in
Clamping - Minimum	0 in
Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Eye Hole	0 in
Diameter - Inside	0 in
Diameter - Outside	1.386 in
Diameter - Pad Bolt	0 in
Length - Pin	0 in
Length Before Compression	21.5 in
Messenger Diameter Range	0 - 0
Take Up	0 in
Thickness - Pad	0 in
Total Adjustment	0 in
Width - Pad	3 in

#### Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

#### Conductor Related

Clamping Range	0- 0
Conductor Compatibility	ACSR-Dipper-1351.5-45/7
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

#### Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
FG-A031561NT-SPEC-EN | REV 6/2024