

# HUBBELL Power Systems

## Compression Deadend, Uni-Grip®(One Die), Full Tension

By FARGO

Catalog # [A040813NT](#)

Full tension deadend assembly for ACSR conductors consists of a prefilled aluminum deadend body precompressed onto a steel eye, prefilled 15° jumper terminals, mounting hardware and core gripping unit.



## Features

- For use with 336.4 kcmil 26/7 ACSR code name Linnet
- Full tension Deadend assembly
- Outside Diameter is 0.720 inches
- Double Tongue
- Steel eye factory compressed in Horizontal orientation
- One Die Compression with die size O8CD
- Material: Body - seamless extruded aluminum alloy tube, Eye - galvanized forged steel, Terminals - seamless extruded aluminum alloy tube, Hardware - aluminum alloy.
- Aluminum deadend body and jumper terminals are prefilled with joint compound
- Uni-Grip Deadends and Jumper Terminals for conductors 1" dia or larger are EHV rated
- Jumper Terminals and mounting hardware included as standard. To omit both jumper terminals, add suffix "NT" to catalog number. Example: A0112451NT.
- To omit both jumper terminals and deadend tongues, add suffix "NPNT" to the catalog number. Example: A0112451NPNT.
- For XL repair deadend, add suffix "XL" and repair cutoff length in inches. Example: A0112451XL24.

## General

Bolt Installation Torque (Recommended)	0 ft-lbs
Compression Method	Uni-Grip (single die system)
Die Size	O8CD
EU RoHS Indicator	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Number of Bolt Holes	2
Number of Pad Holes	0
Press Minimum	12 to
Product Category	Eye
Style	Uni-Grip, Double Tongue, Horizontal Eye
Tension Range	0 lb
Terminal Option	No
Type	Compression
UPC	096359276920

## Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0 °
Clamping - Maximum	0 in
Clamping - Minimum	0 in
Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Eye Hole	0 in
Diameter - Inside	0 in
Diameter - Outside	0.72 in
Diameter - Pad Bolt	0 in
Length - Pin	0 in
Length Before Compression	13.2 in
Messenger Diameter Range	0 - 0
Take Up	0 in
Thickness - Pad	0 in
Total Adjustment	0 in
Weight	2.74 lb
Width - Pad	2 in

## Electrical Ratings

Voltage Application	Standard
---------------------	----------

## Conductor Related

Clamping Range	0- 0
Conductor Compatibility	ACSR-Linnet-336.4-26/7
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

## Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
FG-A040813NT-SPEC-EN | REV 6/2024