

Compression Deadend

By FARGO
Catalog # [A090813NT](#)

Compression Deadend, Uni-Grip, Single Tongue, Adjustable Clevis, for ACSR 336.4 kcmil 26/7, Without Terminal



Features

- For use with ACSR code name Linnet
- Full tension Deadend assembly
- Steel Adjustable Clevis threaded stub factory compressed in deadend
- Prefilled with joint compound
- "NT" suffix eliminates Jumper Terminal & Mounting Hardware

General

| | |
|-------------------------|--|
| Compression Method | Uni-Grip (single die system) |
| Die Size | 08CD |
| Material | Aluminum; Steel |
| Material - Body | Seamless Extruded Aluminum Alloy |
| Material - Clevis | Galvanized Forged Steel |
| Material - Hardware | Aluminum Alloy |
| Material - Pin (Cotter) | #304 Stainless Steel |
| Number of Bolt Holes | 2 |
| Press Minimum | 12 to |
| Product Category | Adjustable Clevis |
| Style | Uni-Grip, Single Tongue, Adjustable Clevis |
| Terminal Option | No |
| Type | Compression |

Dimensions

| | |
|------------------------------|----------|
| Bolt Diameter | 0.620 in |
| Diameter - Clamping Hardware | 0 in |
| Diameter - Outside | 0.72 in |
| Length Before Compression | 19.3 in |
| Maximum Adjustment | 2.9 in |
| Messenger Diameter Range | 0 - 0 |
| Width - Pad | 2 in |

Electrical Ratings

| | |
|---------------------|----------|
| Voltage Application | Standard |
|---------------------|----------|

Conductor Related

| | |
|---------------------------------|------------------------|
| Clamping Range | 0 - 0 |
| Conductor Compatibility | ACSR-Linnet-336.4-26/7 |
| Conductor Diameter (Main) Range | 0 - 0 |

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)