

Compression Deadend

By FARGO
Catalog # A101126NT

Compression Deadend, Uni-Grip, Double Tongue, Adjustable Clevis, for ACSR 556.5 kcmil 30/7, Without Terminals



*Representative Image

Features

- For use with ACSR code name Eagle
- Full tension Deadend assembly
- Steel Adjustable Clevis threaded stub factory compressed in deadend
- Prefilled with joint compound
- Double tongue deadends provided with 2 jumper terminals & mounting hardware
- "NT" suffix eliminates Jumper Terminal & Mounting Hardware

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Compression Method	Uni-Grip (single die system)
Die Size	11CD
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Clevis	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Pin (Cotter)	#304 Stainless Steel
Number of Bolt Holes	4
Number of Pad Holes	0
Press Minimum	60 to
Product Category	Adjustable Clevis
Style	Uni-Grip, Double Tongue, Adjustable Clevis
Tension Range	0 lb
Terminal Option	No
Type	Compression

Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0 °
Bolt Diameter	1.000 in
Clamping - Maximum	0 in
Clamping - Minimum	0 in
Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Eye Hole	0 in
Diameter - Inside	0 in
Diameter - Outside	0.953 in
Diameter - Pad Bolt	0 in
Length - Pin	0 in
Length Before Compression	24.3 in
Maximum Adjustment	3.5 in
Messenger Diameter Range	0 - 0
Take Up	0 in
Thickness - Pad	0 in
Total Adjustment	0 in
Width - Pad	3 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Clamping Range	0- 0
Conductor Compatibility	ACSR-Eagle-556.5-30/7
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
FG-A101126NT-SPEC-EN | REV 9/2023