

# Compression Deadend

By FARGO  
Catalog # [A101021NT](#)

Compression Deadend, Uni-Grip, Double Tongue, Adjustable Clevis, for ACSR 477 kcmil 26/7, Without Terminals



\*Representative Image

## Features

- For use with ACSR code name Hawk
- Full tension Deadend assembly
- Steel Adjustable Clevis threaded stub factory compressed in deadend
- Prefilled with joint compound
- Double tongue deadends provided with 2 jumper terminals & mounting hardware
- "NT" suffix eliminates Jumper Terminal & Mounting Hardware

## General

Compression Method	Uni-Grip (single die system)
Die Size	10CD
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Clevis	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Pin (Cotter)	#304 Stainless Steel
Number of Bolt Holes	2
Press Minimum	60 to
Product Category	Adjustable Clevis
Style	Uni-Grip, Double Tongue, Adjustable Clevis
Terminal Option	No
Type	Compression

## Dimensions

Bolt Diameter	0.750 in
Diameter - Clamping Hardware	0 in
Diameter - Outside	0.858 in
Length Before Compression	21 in
Maximum Adjustment	2.8 in
Messenger Diameter Range	0 - 0
Width - Pad	2 in

## Electrical Ratings

Voltage Application	Standard
---------------------	----------

## Conductor Related

Clamping Range	0- 0
Conductor Compatibility	ACSR-Hawk-477-26/7
Conductor Diameter (Main) Range	0 - 0

## Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)

