

Compression Deadend

By FARGO
Catalog # [A101663](#)

Compression Deadend, Uni-Grip, Double Tongue, Adjustable Clevis, for ACSR 1431 kcmil 45/7, With Terminals



*Representative Image

Features

- For use with ACSR code name Bobolink
- Full tension Deadend assembly
- Steel Adjustable Clevis threaded stub factory compressed in deadend
- Prefilled with joint compound
- Double tongue deadends provided with 2 jumper terminals & mounting hardware
- Jumper Terminal & Mounting Hardware included

General

Compression Method	Uni-Grip (single die system)
Die Size	16CD
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Clevis	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Pin (Cotter)	#304 Stainless Steel
Material - Terminal	Seamless Extruded Aluminum Alloy
Number of Bolt Holes	4
Press Minimum	60 to
Product Category	Adjustable Clevis
Style	Uni-Grip, Double Tongue, Adjustable Clevis
Type	Compression

Dimensions

Bolt Diameter	1.100 in
Diameter - Clamping Hardware	0 in
Diameter - Outside	1.427 in
Length Before Compression	33.9 in
Maximum Adjustment	4.4 in
Messenger Diameter Range	0 - 0
Width - Pad	3 in

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Clamping Range	0 - 0
Conductor Compatibility	ACSR-Bobolink-1431-45/7
Conductor Diameter (Main) Range	0 - 0

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)