

## Compression Deadend

By FARGO  
Catalog # [A101030](#)

Compression Deadend, Uni-Grip, Double Tongue, Adjustable Clevis, for ACSR 636 kcmil 36/1, With Terminals



\*Representative Image

### Features

- For use with ACSR code name Swift
- Full tension Deadend assembly
- Steel Adjustable Clevis threaded stub factory compressed in deadend
- Prefilled with joint compound
- Double tongue deadends provided with 2 jumper terminals & mounting hardware
- Jumper Terminal & Mounting Hardware included

### General

Compression Method	Uni-Grip (single die system)
Die Size	10CD
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Clevis	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Pin (Cotter)	#304 Stainless Steel
Material - Terminal	Seamless Extruded Aluminum Alloy
Number of Bolt Holes	2
Press Minimum	60 to
Product Category	Adjustable Clevis
Style	Uni-Grip, Double Tongue, Adjustable Clevis
Type	Compression

### Dimensions

Bolt Diameter	0.750 in
Diameter - Clamping Hardware	0 in
Diameter - Outside	0.93 in
Length Before Compression	21 in
Maximum Adjustment	2.8 in
Messenger Diameter Range	0 - 0
Width - Pad	2 in

### Electrical Ratings

Voltage Application	Standard
---------------------	----------

### Conductor Related

Clamping Range	0 - 0
Conductor Compatibility	ACSR-Swift-636-36/1
Conductor Diameter (Main) Range	0 - 0

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)