

HUBBELL
Power Systems

Compression Deadend, Uni-Grip®(One Die), Full Tension

By FARGO
Catalog # [A101234NT](#)



Features

-
-
-
-
-
-
-
-
-
-
-
-
-
-
-
-
-
-
-
-
-

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Compression Method	Uni-Grip (single die system)
Die Size	12CD
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Clevis	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Pin (Cotter)	#304 Stainless Steel
Number of Bolt Holes	4
Number of Pad Holes	0
Press Minimum	60 to
Product Category	Adjustable Clevis
Style	Uni-Grip, Double Tongue, Adjustable Clevis
Tension Range	0 lb
Terminal Option	No
Type	Compression

Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0 °
Bolt Diameter	1 in
Clamping - Maximum	0 in
Clamping - Minimum	0 in
Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Eye Hole	0 in
Diameter - Inside	0 in
Diameter - Outside	1.019 in
Diameter - Pad Bolt	0 in
Length - Pin	0 in
Length Before Compression	25.2 in
Maximum Adjustment	3.5 in
Messenger Diameter Range	0 - 0
Take Up	0 in
Thickness - Pad	0 in
Total Adjustment	0 in
Width - Pad	3 in

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Clamping Range	0- 0
Conductor Compatibility	ACSR-Egret-636-30/19
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-A101234NT-SPEC-EN | REV 6/2024