

HUBBELL

Power Systems

Compression Splice Uni-Grip®(One Die) Full Tension

By FARGO
Catalog # [A151234](#)



A full-tension compression splice assembly for ACSR conductor consists of a prefilled aluminum body and two core wire gripping units.

*Representative Image

Features

- For use with 636.0 kcmil 30/19 ACSR code name Egret
- Full tension splice assembly
- Outside Diameter is 1.019 inches
- One Die Compression with die size 12CD
- Material: Body – seamless extruded aluminum alloy tube, Gripping Unit – aluminum alloy
- Splices are prefilled with inhibitor and barrel ends plugged.
- For Extra Length repair splice Add "XL" suffix and repair cutoff length in Inches. Example: A151128XL24
- Splices are EHV rated where conductor dia. is 1" or larger.

General

Compression Method	Uni-Grip (single die system)
Die Size	12CD
Material	Aluminum Alloy
Press Minimum	60 to
Tension Range	0 lb

Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Diameter - Outside	1.019 in
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	21.6 in
Messenger Diameter Range	0 - 0
Weight	3.263 lb

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Conductor Compatibility	ACSR-Egret-636-30/19
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSR
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Certifications And Compliance

UL Listed	No
-----------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-A151234-SPEC-EN | REV 6/2024