

# HUBBELL

## Power Systems

### Compression Splice Uni-Grip® (One Die) Full Tension

By FARGO  
Catalog # [AB151313](#)



A full-tension compression splice assembly for AAAC and ACAR conductors consist of a prefilled aluminum body.

#### Features

- For use with AAAC and ACAR conductor range 1000.0 - 1127.0 Kcmil
- Conductor Outside Diameter Range: 1.140 - 1.235 inches
- Full tension splice assembly
- One Die Compression with die size 13CD
- Material: Body - seamless extruded aluminum alloy tube
- Splices are prefilled with inhibitor and barrel ends plugged.
- For Extra Length repair splice Add "XL" suffix and repair cutoff length in Inches. Example: AB151010XL24
- Splices are EHV rated where conductor dia. is 1" or larger.

#### General

Compression Method	Uni-Grip (single die system)
Die Size	13CD
EU RoHS Indicator	No
Material	Aluminum Alloy
Press Minimum	60 to
Tension Range	0 lb
UPC	096359511045

#### Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	23.4 in
Messenger Diameter Range	0 - 0
Weight	5.39 lb

#### Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

#### Conductor Related

Conductor Compatibility	ACAR-1024.5-30/7;ACAR-1081-18/19;ACAR-1109-30/7
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	1.235 in
Conductor Diameter - Minimum	1.141 in
Conductor Diameter Range	1.141 - 1.235
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

#### Certifications And Compliance

UL Listed	No
-----------	----

#### Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
FG-AB151313-SPEC-EN | REV 6/2024