

Compression Splice Uni-Grip® (One Die) Full Tension

By FARGO
Catalog # [AB151212](#)



A full-tension compression splice assebmly for AAAC and ACAR conductors consist of a prefilled aluminum body.

Features

- For use with AAAC and ACAR conductor range 833.6 - 932.6 Kcmil
- Conductor Outside Diameter Range: 1.026 - 1.131 inches
- Full tension splice assembly
- One Die Compression with die size 12CD
- Material: Body – seamless extruded aluminum alloy tube
- Splices are prefilled with inhibitor and barrel ends plugged.
- For Extra Length repair splice Add "XL" suffix and repair cutoff length in Inches. Example: AB151010XL24
- Splices are EHV rated where conductor dia. is 1" or larger.

General

Catalog Number	AB151212
Compression Method	Uni-Grip (single die system)
Die Size	12CD
EU RoHS Indicator	No
Material	Aluminum Alloy
Press Minimum	60 to
Tension Range	0 lb
UPC	096359465508

Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Insulator / Conductor Hole	0 in
Spacing	
Length Before Compression	21.6 in
Messenger Diameter Range	0 - 0

Weight	3.342 lb
--------	----------

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Conductor Compatibility	ACAR-853.7-30/7
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	1.14 in
Conductor Diameter - Minimum	1.046 in
Conductor Diameter Range	1.046 - 1.14
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
UL Listed	No

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Specifications - AB151212](#)