

Compression Deadend

By FARGO
Catalog # [C091818](#)

Compression Deadend, Uni-Grip, Single Tongue, Adjustable Clevis, for AAC, Dia. Range 1.602 - 1.681, With Terminals



*Representative Image

Features

- For use with AAC code names: Cowslip
- Full tension Deadend assembly
- Steel Adjustable Clevis threaded stub factory compressed in deadend
- Prefilled with joint compound
- Jumper Terminal & Mounting Hardware included

General

Compression Method	Uni-Grip (single die system)
Die Size	18CD
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Clevis	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Pin (Cotter)	#304 Stainless Steel
Material - Terminal	Seamless Extruded Aluminum Alloy
Number of Bolt Holes	4
Press Minimum	100 to
Product Category	Adjustable Clevis
Style	Uni-Grip, Single Tongue, Adjustable Clevis
Type	Compression

Dimensions

Bolt Diameter	1.100 in
Diameter - Clamping Hardware	0 in
Length Before Compression	30.4 in
Maximum Adjustment	4.4 in
Messenger Diameter Range	0 - 0
Width - Pad	4 in

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Clamping Range	0 - 0
Conductor Compatibility	AAC-Cowslip-2000-91
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	1.71 in
Conductor Diameter - Minimum	1.616 in
Conductor Diameter Range	1.616 - 1.71

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)