

Compression Deadend

By FARGO
Catalog # C101111

Compression Deadend, Uni-Grip, Double Tongue, Adjustable Clevis, for AAC, Dia. Range 0.951 - 1.045, With Terminals



*Representative Image

Features

- For use with AAC code names: Verbena, Flag, Violet, Nasturtium, Petunia, Cattail, Arbutus, Lilac, Fuchsia, Heliotrope
- Full tension Deadend assembly
- Steel Adjustable Clevis threaded stub factory compressed in deadend
- Prefilled with joint compound
- Jumper Terminal & Mounting Hardware included

General

Compression Method	Uni-Grip (single die system)
Die Size	11CD
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Clevis	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Pin (Cotter)	#304 Stainless Steel
Material - Terminal	Seamless Extruded Aluminum Alloy
Number of Bolt Holes	4
Press Minimum	60 to
Product Category	Adjustable Clevis
Style	Uni-Grip, Double Tongue, Adjustable Clevis
Type	Compression

Dimensions

Bolt Diameter	1.000 in
Diameter - Clamping Hardware	0 in
Length Before Compression	21 in
Maximum Adjustment	3.5 in
Messenger Diameter Range	0 - 0
Width - Pad	3 in

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Clamping Range	0 - 0
Conductor Compatibility	AAC-Flag-700-61; AAC-Violet-715.5-37; AAC-Nasturtium-715.5-61; AAC-Cattail-750-61; AAC-Arbutus-795-37; AAC-Lilac-795-61
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	1.045 in
Conductor Diameter - Minimum	0.951 in
Conductor Diameter Range	0.951 - 1.045

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)

